


1.View and size(视图及尺寸)

Main technical indicators(主要技术指标)	
1.Mating (插拔次数)	5000
2.Working Temperature (温度)	-55~+150 ℃
3.IP Rating (防护级别)	IP 50
4.Diameter of socket end(插合端直径)	φ0.7
5.Testing Voltage (测试电压)	950V
6.Working Voltage (工作电压)	1150V
7.Rated Current (额定电流)	2A
8.Shell material(壳体材质)	Brass (chromium plating)/(nickel plating) fixation ring/ 黄铜 (镀铬) /(镀镍) 固定圈
9.Pin Material(插针材料)	Copper alloy gold plating(铜合金镀金)
10. Insulator material(绝缘体材质)	PPS


Sum up(总结)	
Series(系列)	B
Shell style/model (外壳样式/型号)	ZPG: Elbow receptacle for printed circuit (solder or screw fixing) /印刷电路用弯头插座, 焊接或螺丝固定
Button (按键)	A button(一个按键)
Termination type (终止类型)	Female print 90°PCB(印刷90° PCB)
Line diameter awg(线材直径)	20AWG-28AWG
Cable diameterφ (电缆直径)	0-0
Match plug(匹配插头)	TGG.1B.P08.CLAD52H

Location pin combination (定位销组合)				
Series(系列)	Number of positioning pins(定位销数量)	Angle(角度)	Series(系列)-1B	
G	One(1)	A	(Zero degrees)0°	
A	Two(2)		Thirty degrees(30°)	
B	Two(2)		Sixty degrees(60°)	
C	Two(2)		Ninety degrees(90°)	
D	Two(2)	β	135 degrees(135°)	
E	Two(2)		145 degrees(145°)	
F	Two(2)		155 degrees(155°)	
J	Two(2)	Y	Forty-five degrees(45°)	
K	Two(2)		Seventy degrees(70°)	
L	Two(2)		80 degrees(80°)	


	A	B	C√	ANGLE	
5-10	±0.02	±0.05	±0.1	0°-30°	±0.1°
50-100	±0.1	±0.15	±0.2	61°-90°	±0.5°
50-100	±0.15	±0.2	±0.25		
100-	±0.15%	±0.20%	±0.25%		




	A	L	K	C	M
MM	11	27.0	13.3	14	3.2
in	0.433	1.063	0.5236	0.5512	0.126




Pcb plate opening size
(PCB板开孔尺寸)



M-directional layout
(M向排版位)



Boarded mother adhesive core
(板接型母胶芯)



Positive view of the socket
(插座正视图)

ZPG.1B.P08.H.L.N

Model(型号)
Positioning pin(定位销)
Series(系列)
Needle core configuration(针芯配置)
Outer casing(外壳)
Insulator(绝缘体)
Needle core(针芯)

DESIGNED (设计)		DATE(日期)		SCALE(比例)	N/A(不适用)	MODEL TYPE 型号类型: ZPG.1B.P08.H.L.N
CHECKED (校对)		DATE(日期)		VIEW(视图)		PART NO. 1B8 core socket 名称: 1B8芯插座
APPROVED (审核)		DATE(日期)		UNIT(单位)	MM	DWG NO.:
REVISIONS				MATERIAL (材料)		
www.helloxb.com www.helloxb.cn				XKB INDUSTRIAL PRECISION CO.,LIMITED		WEIGHT(重量) SHEET(张) REVISION(修订)
						1/1 A0