




color B:Black W:White

Model No.	PJ-317BA-X	PJ-317B-X	PJ-317B1-X	PJ-317B9A-X	PJ-317B9B-X
Schematic					
Pin	sleeve	sleeve	sleeve	sleeve	sleeve
1	sleeve	sleeve	sleeve	sleeve	sleeve
2	tip	tip	tip	tip	tip
3	ring	ring	ring	ring	NP
10	tip switch	NP	tip switch	NP	tip switch
11	NP	ring switch	ring switch	NP	NP

Plastic	PBT	
insulator	PA66	
contact clip	C5210R-EH	
spring	Stainless steel	
Terminal 11	Brass	tin
Terminal 10	Brass	tin
Terminal 9	Brass	tin
Terminal 8	Brass	tin
Terminal 7	Brass	tin
Terminal 6	Brass	tin
Terminal 5	Brass	tin
Terminal 4	Brass	tin
Terminal 3	Phosphor Bronze	tin
Terminal 2	Phosphor Bronze	tin
Terminal 1	Phosphor Bronze	tin
PAPT NAMF	MATERIAL	PLATING

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:	MODEL TYPE: 3.5 PHONE JACK
CHECKED		UNIT: mm/in	PART NO.: PJ-317B1-B
APPROVED		SIZE: A4	DWG NO.: X-PJ-317B1-B
XKB INDUSTRIAL PRECISION CO.,LIMITED		SCALE	PAGE
		N/A	1/1
		REVISION	A1