





REVISION RECORD				
REV	ECN.	DESCRIPTION	DRFT	DATE

NOTE 1:
UL标准 (UL Standard)
1. 额定电压与电流: 300V/15A
Rated voltage/Rated current: 300V/15A
2. 功频耐压: AC1600V/Min
Withstanding Voltage: AC1600V/Min
IEC标准 (IEC Standard)
1. 额定电压与电流: 320V/20A
Rated voltage/Rated current: 320V/20A
NOTE 2:
1. 间距 (Pitch): 5.08mm
2. 使用温度范围: $-40^{\circ}\text{C} \sim +105^{\circ}\text{C}$
Operating temperature: $-40^{\circ}\text{C} \sim +105^{\circ}\text{C}$
3. 符合RoSH环保要求
RoHS Compliance
5. 未标注公差表
Undimensioned tolerances

P距方向公差 (mm)			其他尺寸公差 (mm)					
Pitch range in mm			Nominal dimension range in mm					
≤ 6	6 ~ 10	10 ~ 24	≤ 30	30 ~ 60	60 ~ 100	100 ~ 150	> 150	0.1/10
± 0.15	± 0.20	± 0.30	± 0.20	± 0.30	± 0.50	± 0.70	± 1.00	$\pm 1^{\circ}$

订购方式 (HOW TO ORDER)
MX2EDGV-5.08-□□P-□-□-□□□□
Series NO. Pitch Poles 客户型号 Customer Request
颜色 (Color)
1. 单间距 Single Pitch 2. 蓝色 (Blue)
2. 双间距 Double Pitch 3. 黑色 (Black) 4. 绿色 (Green)
5. 橙色 (Orange) 6. 红色 (Red)
7. 黄色 (Yellow) 8. 白色 (White)
9. 透明 (Transparent)

N=No.of contacts

<table><tr><td>2</td><td>(Pin header)焊脚</td><td>(Copper alloy) 铜合金</td><td>(Sn plated)镀锡</td></tr><tr><td>1</td><td>(Housing)塑件</td><td>PA66</td><td>UL94V-0</td></tr><tr><td>ITEM</td><td>NAME OF PART</td><td>MATERIAL</td><td>NOTES</td></tr></table>				2	(Pin header)焊脚	(Copper alloy) 铜合金	(Sn plated)镀锡	1	(Housing)塑件	PA66	UL94V-0	ITEM	NAME OF PART	MATERIAL	NOTES	PART NO.: /		 安徽亿思特电子科技有限公司 ANHUI EAST ELECTRONIC TECHNOLOGY CO., LTD.			
				2	(Pin header)焊脚	(Copper alloy) 铜合金	(Sn plated)镀锡														
				1	(Housing)塑件	PA66	UL94V-0														
				ITEM	NAME OF PART	MATERIAL	NOTES														
				APPD: /																	
CHKD: /		型号	MX2EDGV-5.08-XXP-1X																		
DRFT: /																					
 THIED ANGLE PROJECTION																					
		系列	MX2EDGV-5.08		页码	1/1															
		图号	MX2EDGV508001		比例	1:1															