







PCB LAYOUT

Specifications:

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating: 2A AC/DC

额定电流: 2A AC/DC

Withstanding voltage:1500V AC/minute

耐压电压: 1500V AC/分钟

Temperature range:-25℃~+85℃

温度范围: -25℃~+85℃

Insulation resistance:≥1000MΩ

绝缘电阻: ≥1000MΩ

Contact resistance: ≤20mΩ

接触电阻: ≤20mΩ

Linetype:AWG#22 AWG#24 AWG#26 AWG#28

X9254 W R - 06 -N0 SN

① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

①Series No.

②Category: W-WAFER

③Welding Board Angle: R-Right Angle 90°

④Welding Way: Blank-DIP

⑤Row No.-Pin No.: XX-02P~30P

⑥Plug the Pin & Special No.

⑦Material: N0 -PA66 94V-0

⑧Plating Category: SN-Bright Tin Plating

⑨Color : Blank-Natural Color

Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
2	2.54	5.08	10	22.86	25.40
3	5.08	7.62	11	25.40	27.94
4	7.62	10.16	12	27.94	30.48
5	10.16	12.70	13	30.48	33.02
6	12.70	15.24	14	33.02	35.56
7	15.24	17.78	15	35.56	73.66
8	17.78	20.32	30	73.66	76.20
9	20.32	22.86			

X9254WR-06-N0SN	Nylon 66 UL 94V-0	Brass	Tin-Plated	X9254H
PART N0	Material	Material(Pin)	Finish(Pin)	Suitable XKB Housing

							DSND		DATE		SCALE: N/A	MODEL TYPE: 2.54mm Crimp Style Connectors						
Δx					ANGLAR	±5°	DWN		DATE		VIEW: 	PART NO.: X9254WR-06-N0SN						
Δx					L ≤ 4	±0.2	CHKD		DATE		UNIT: mm/in	DWG NO.: X-X9254WR-06-N0SN						
Δx					4<L ≤ 16	±0.3	APPD		DATE		SIZE: A4							
Δx					16<L ≤ 63	±0.4	XKB INDUSTRIAL PRECISION CO.,LIMITED						WEIGHT 1.0g	SHEET 1/1	REVISION A0			
MARK	DESCRIPTION				DATE	REVISED							APPROVED	L > 63	±0.5			
REVISIONS													UNSPECIFIED TOLERANCES					
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn																		