

1

2

3

4

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2024.05.09	

规格 Specification:

1.额定值 Rating:6A 125/250VAC

2.接触电阻 Contact resistance:≤30 mΩ

3.绝缘电阻 Insulation resistance:≥100 MΩ(DC500V/Min)

4.电气寿命 Electronics life:>10000 cycles



5.操作力 Operation force:350±150gf

6.所有材料符合Rohs要求 All materials are Rohs compliant

PART NO.:

SS-X 06 26 P G-5 N 1 W W
① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨ ⑩ ⑪

- ① SS: XKB Vertical handle;
- ② Enclosure Material:
A-Metal case;
BLANK-Plastic case;
- ③ Current Rating: 06-6A;
- ④ Switch Circuit:26-2P6T;
- ⑤ P: Welding plates;
- ⑥ Handle Shape: G-Camber handle;
- ⑦ Handle Height: 3~15mm;
- ⑧ Enclosure Shape:N-Square enclosure;
- ⑨ Terminal specs:
1:TYPE-1; 2:TYPE-2; 3:TYPE-3;
4:TYPE-4; 5:TYPE-5;
- ⑩ Handle Colour:
B-Black; W-White; R-Red
- ⑪ Housing Colour:
B-Black; W-White; R-Red




CIRCUIT







产品字码标识

ANGULAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



XKB INDUSTRIAL PRECISION CO.,LIMITED

DESIGN	桑 葚	VIEW:	 MODEL TYPE: SLIDE SWITCH		
CHECKED		UNIT: mm/in	PART NO.: SS-0626PG-5N1WW		
APPROVED		SIZE: A4	DWG NO.: X-SS-0626PG-5N1WW		
PRECISION CO.,LIMITED			SCALE	PAGE	REVISION
			N/A	1/1	A0



PCB LAYOUT