




■ Specifications :

- Voltage rating: 50V AC / DC
- Current rating: 2A AC / DC
- Withstanding voltage: 500V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance:≥100MΩ
- Contact resistance:≤20mΩ
- After environmental testing:≤40mΩ

X1224H-02-N0

① ② ③ ④

- ① Series No.
② Category:H-HSG
③ Row No.Pin No.XX-02P-10P
④ Material:N0-PA66 94V-0

Poles	Dimensions(mm)		
	A	B	C
2	1.20	2.60	3.10
3	2.40	3.80	4.30
4	3.60	5.00	5.50
5	4.80	6.20	6.70
6	6.00	7.40	7.90
7	7.20	8.60	9.10
8	8.40	9.80	10.30
9	9.60	11.00	11.50
10	10.80	12.20	12.70

X1224H-02-N0	N0-PA66 94V-0	X1224T	X1224T
PART NO	Material	Suitable XKB Terminal	Suitable XKB Terminal

							DSND		DATE		SCALE: N/A	MODEL TYPE: 1.2mm Crimp Style Connectors				
Δx					ANGLAR	±5°	DWN		DATE		VIEW: 	PART NO.: X1224H-02-N0				
Δx					L ≤ 4	±0.2	CHKD		DATE		UNIT: mm/in	DWG NO.: X-X1224H-02-N0				
Δx					4<L ≤ 16	±0.3	APPD		DATE		SIZE: A4	WEIGHT	SHEET	REVISION		
Δx					16<L ≤ 63	±0.4	XKB INDUSTRIAL PRECISION CO.,LIMITED							1.0g	1/1	A0
MARK	DESCRIPTION				DATE	REVISED								APPROVED	L > 63	±0.5
REVISIONS																
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn																