




Specifications :

- Voltage rating: 250V AC / DC
- Current rating: 3A AC / DC
- Withstanding voltage: 1000V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance: $\geq 1000M\Omega$
- Contact resistance: $\leq 10m\Omega$
- After environmental testing : $\leq 20m\Omega$

X2564 H 03- N0
① ② ③ ④

- ① Series No.
② Category : H-HSG
③ Appearance type:Blank-Ordinary
④ Row No.-Pin No.: XX-02P~16P
⑤ Material : N0-PA66 94V-0

Poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	C		A	B	C
02	2.50	7.50	5.90	12	27.50	32.50	30.90
03	5.00	10.00	8.40	13	30.00	35.00	33.40
04	7.50	12.50	10.90	14	32.50	37.50	35.90
05	10.00	15.00	13.40	15	35.00	40.00	38.40
06	12.50	17.50	15.90	16	37.50	42.50	40.90
07	15.00	20.00	18.40				
08	17.50	22.50	20.90				
09	20.00	25.00	23.40				
10	22.50	27.50	25.90				
11	25.00	30.00	28.40				

X2564H-03-N0	Nyoln 66 UL 94V-0	X2564T	X2564W
PART NO	Material	Suitable XKB Terminal	Suitable XKB Wafer

							DSND		DATE		SCALE: N/A	MODEL TYPE: 2.5mm Crimp Style Connectors		
Δx					ANGLAR	±5°	DWN		DATE		VIEW: 	PART NO.: X2564H-03-N0		
Δx					4<L≤16	±0.3	CHKD		DATE		UNIT: mm/in	DWG NO.: X-X2564H-03-N0		
Δx					16<L≤63	±0.4	APPD		DATE		SIZE: A4			
MARK	DESCRIPTION			DATE	REVISED	APPROVED						L>63	±0.5	
REVISIONS							UNSPECIFIED TOLERANCES					XKB INDUSTRIAL PRECISION CO.,LIMITED		
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn														
												WEIGHT	SHEET	REVISION
												1.0g	1/1	A0