








Specifications:

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating:3A AC/DC

额定电流: 3A AC/DC

Withstanding voltage:800V AC/minute

耐受电压: 800V AC/分钟

Temperature range:-25℃~+85℃

温度范围: -25℃~+85℃

Insulation resistance:1000MΩ min

绝缘电阻: 1000MΩ Min

Contact resistance:30mΩ Max

接触电阻: 30mΩ Max

X8826 H - 2x07 - N0
① ② ③ ④

1.Series No

2.Category:H-HSG

3.Row No.Pin No:2xXX-2x02~2x20P

4.Material:N0-PA66 UL94V-0

Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
2x02	2.50	7.50	2x08	17.50	22.50
2x03	5.00	10.00	2x09	20.00	25.00
2x04	7.50	12.50	2x10	22.50	27.50
2x05	10.00	15.00	2x11	25.00	30.00
2x06	12.50	17.50	2x12	27.50	32.50
2x07	15.00	20.00	2x20	47.50	52.50

X8826H-2x07-N0	PA66	X8826W	X8826T
PART NO	Material	Suitable XKB Wafer	Suitable XKB Terminal

DSND		SCALE: N/A	MODEL TYPE: 2.5mm Crimp Style Connector
DWN		VIEW:	PART NO.: X8826H-2x07-N0
CHKD		UNIT: mm/in	DWG NO.: X-X8826H-2x07-N0
APPD		SIZE: A4	

					ANGULAR	±5°
ΔX					L≤ 4	±0.2
ΔX					4<L≤ 16	±0.3
ΔX					16<L≤ 63	±0.4
MARK					L> 63	±0.5
DESCRIPTION					DATE	REVISED
REVISIONS					APPROVED	UNSPECIFIED TOLERANCES
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						

XKB

XKB INDUSTRIAL PRECISION CO.,LIMITED

WEIGHT	SHEET	REVISION
	1/1	A0