







P.C.B LAYOUT



Specifications:

规格:

Voltage rating:150V AC/DC

额定电压: 150V AC/DC

Current rating:1A AC/DC

额定电流: 1A AC/DC

Withstanding voltage:500V AC/minute

耐受电压: 500V AC/分钟

Temperature range:-25℃~+85℃

温度范围: -25℃~+85℃

Insulation resistance:500MΩ min

绝缘电阻: 500MΩ Min

Contact resistance:30mΩ Max

接触电阻: 30mΩ Max

X9862 W V S -14 A -6T SN  
① ② ③ ④ ⑤ ⑥ ⑦ ⑧

- 1.Series No
- 2.Category :W-Wafer
- 3.Welding Board Angle:V-Straight 180°
- 4.Welding Way:S-SMT
- 5.Row No.Pin No:XX-02P-30P
- 6.Special No: A-With Lock
- 7.Material: 6T-PA6T UL94V-0 Beige
- 8.Plating:SN- Tin Plating

| Poles | Dimensions(mm) |       |
|-------|----------------|-------|
|       | A              | B     |
| 02    | 1.25           | 7.45  |
| 03    | 2.50           | 8.70  |
| 04    | 3.75           | 9.95  |
| 05    | 5.00           | 11.20 |
| 06    | 6.25           | 12.45 |
| 07    | 7.50           | 13.70 |
| 08    | 8.75           | 14.95 |
| 09    | 10.00          | 16.20 |
| 10    | 11.25          | 17.45 |
| 11    | 12.50          | 18.70 |
| 12    | 13.75          | 19.95 |
| 13    | 15.00          | 21.20 |
| 14    | 16.25          | 22.45 |
| 15    | 17.50          | 23.70 |
| 20    | 23.75          | 29.95 |
| 25    | 25.00          | 36.20 |
| 30    | 36.25          | 42.45 |

|                   |          |               |                      |
|-------------------|----------|---------------|----------------------|
| X9862WVS-14A-6TSN | PA6T     | Brass         | X9862H-A             |
| PART NO           | Material | Material(Pin) | Suitable XKB Housing |

|                                                     |             |      |         |          |                        |      |
|-----------------------------------------------------|-------------|------|---------|----------|------------------------|------|
|                                                     |             |      |         |          | ANGLAR                 | ±5°  |
| Δx                                                  |             |      |         |          | L≤ 4                   | ±0.2 |
| Δx                                                  |             |      |         |          | 4<L≤ 16                | ±0.3 |
| Δx                                                  |             |      |         |          | 16<L≤ 63               | ±0.4 |
| MARK                                                | DESCRIPTION | DATE | REVISED | APPROVED | L> 63                  | ±0.5 |
| REVISIONS                                           |             |      |         |          | UNSPECIFIED TOLERANCES |      |
| www.helloxkb.com    www.helloxkb.cn    www.xk-dg.cn |             |      |         |          |                        |      |

XKB

XKB INDUSTRIAL PRECISION CO.,LIMITED

|      |  |             |                                             |
|------|--|-------------|---------------------------------------------|
| DSND |  | SCALE: N/A  | MODEL TYPE:<br>1.25mm Crimp Style Connector |
| DWN  |  | VIEW:       | PART NO.:<br>X9862WVS-14A-6TSN              |
| CHKD |  | UNIT: mm/in | DWG NO.:<br>X-X9862WVS-14A-6TSN             |
| APPD |  | SIZE: A4    |                                             |
|      |  | WEIGHT      | SHEET                                       |
|      |  |             | 1/1                                         |
|      |  | REVISION    | A0                                          |