






■ Specifications :

- Voltage rating: 50V AC / DC
- Current rating: 2A AC / DC
- Withstanding voltage: 500V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance:≥100MΩ
- Contact resistance:≤20mΩ
- After environmental testing:≤40mΩ

X1224 WRS-04-LP V01
① ② ③ ④ ⑤ ⑥ ⑦

- ① Series No.
② Category:W-WAFER
③ Wedding Board Angle : R-Right 90°
④ Welding Way:S-SMT
⑤ Row No.Pin No.:XX-04P~07P
⑥ Material:LP-LCP 94V-0;4T-PA4T
⑦ Planting Category: V01-All Gold Flash

Poles	Dimensuons(mm)		
	A	B	C
02	1.20	4.20	2.65
03	2.40	5.40	3.85
04	3.60	6.60	5.05
05	4.80	7.80	6.25
06	6.00	9.00	7.45
07	7.20	10.20	8.65
10	10.80	13.80	12.25



X1224WRS-04-4TV01	PA4T UL 94V-0	Phosphor Bronze	Gold-Flash	X1224T
X1224WRS-04-LPV01	LCP UL 94V-0	Phosphor Bronze	Gold-Flash	
PART NO	Material	Material(Pin And Solder Tabs)	Finish(Pin And Solder Tabs)	Suitable XKB Terminal

							DSND		DATE		SCALE: N/A	MODEL TYPE: 1.20mm Crimp Style Connectors				
Δx					ANGULAR	±5°	DWN		DATE		VIEW: 	PART NO.: X1224WRS-04-LPV01				
Δx					L ≤ 4	±0.2	CHKD		DATE		UNIT: mm/in	DWG NO.: X-X1224WRS-04-LPV01				
Δx					4<L ≤ 16	±0.3	APPD		DATE		SIZE: A4					
Δx					16<L ≤ 63	±0.4										
MARK	DESCRIPTION				DATE	REVISED	APPROVED	L > 63		±0.5						
REVISIONS							UNSPECIFIED TOLERANCES							XKB INDUSTRIAL PRECISION CO.,LIMITED		
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn																
												WEIGHT	SHEET	REVISION		
												1.0g	1/1	A0		