








3D图示 (参考)



PCB安装尺寸图

Specifications :

- 1.Voltage rating: 250V AC / DC
- 2.Current rating: 5A AC / DC
- 3.Withstanding voltage: 1500V AC/minute
- 4.Temperature range: -25°C~+85°C
- 5.Insulation resistance: $\geq 1000M \Omega$
- 6.Contact resistance: 0.02Ω Max
- 7.Material: Nylon 66
Contact Pin: Brass

X5080 W R -04 A- N0 SN
① ② ③ ④ ⑤ ⑥ ⑦

- ① Series No.
- ② Category : W-WAFER
- ③ Wedding Board Angle : R-Straight 90°
- ④ Row No.Pin No.XX-02-12
- ⑤ Special No.A-There are gaps
- ⑥ Material:N0-Nylon66 94V-0
- ⑦ Planting Category:SN-Bright tin plating

PIN	A	B
2	5.08	10.16
3	10.16	15.24
4	15.24	20.32
5	20.32	25.40
6	25.40	30.48
7	30.48	35.56
8	35.56	40.64
9	40.64	45.72
10	45.72	50.80
11	50.80	55.88
12	55.88	60.96

X5080WR-04A-NOS	Nylon66 UL 94V-0	Brass	Tin-Plated	X5080H
PART NO	Material	Material(Pin)	Finsh(Pin)	Suitable XKB Housing

					ANGLAR	±5°
Δx					L≤ 4	±0.2
Δx					4<L≤ 16	±0.3
Δx					16<L≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L> 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						

XKB

XKB INDUSTRIAL PRECISION CO.,LIMITED

DSND	SCALE: N/A	MODEL TYPE:
DWN	VIEW:	5.08mm Crimp Style Connectors
CHKD	UNIT: mm/in	PART NO.: X5080WR-04A-N0SN
APPD	SIZE: A4	DWG NO.: X-X5080WR-04A-N0SN
		WEIGHT
		SHEET
		REVISION
		1/1
		A0