










由 AUTODESK 学生版生成



Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
2*01	---	5.60	2*07	25.20	30.80
2*02	4.20	9.80	2*08	29.40	35.00
2*03	8.40	14.00	2*09	33.60	39.20
2*04	12.60	18.20	2*10	37.80	43.40
2*05	16.80	22.40	2*11	42.00	47.60
2*06	21.00	26.60	2*12	46.20	51.80



Specifications:
规格: XKB
Voltage rating:600V AC/DC
额定电压: 600V AC/DC
Current rating:9A AC/DC
额定电流: 9A AC/DC
Withstanding voltage:1500V AC/minute
耐受电压: 1500V AC/分钟
Temperature range:-25℃~+85℃
温度范围: -25℃~+85℃
Insulation resistance:≥1000MΩ
绝缘电阻: ≥1000MΩ
Contact resistance:≤10mΩ
接触电阻: ≤10mΩ XKB
After environmental testing:≤20mΩ
环境测试后: ≤20兆欧

X9357 H F -2x05 G-N2
① ② ③ ④ ⑤ ⑥ ⑦

- ① Series No.
② Category:H-HSG
③ Welding Board Angle:F-Female
④ Row No.-Pin No.:2*XX-2*01P~2*12P
⑤ Plug the Pin & special No.:
I-Without the Wing; G-With the Wing
⑥ Material:N0-PA66 94V-0;N2-PA66 94V-2
⑦ Color:Blank-Natural Color BK-Black

X9357HF-2x05-N2BK	Nylon 66 94V-2 Black	X9357TM	X9357W Or 9357H	Without Ears
X9357HF-2x05G-N2	Nylon 66 94V-2			With Ears
X9357HF-2x05I-N2	Nylon 66 94V-2			Without Ears
X9357HF-2x05G-N0	Nylon 66 94V-0			With Ears
X9357HF-2x05I-N0	Nylon 66 94V-0			Without Ears
PART NO	Material	Suitable XKB Terminal	Suitable XKB Housing	Note

					XKB	DSND		DATE		SCALE: N/A	MODEL TYPE: 2.40mm Crimp Style Connectors		
						DWN		DATE		VIEW:	PART NO.: X9357HF-2x05G-N2		
						CHKD		DATE		UNIT: mm/in	DWG NO.: X-X9357HF-2x05G-N2		
						APPD		DATE		SIZE: A4			
REVISIONS					UNSPECIFIED TOLERANCES					WEIGHT		SHEET	REVISION
										1.0g		1/1	A0