





Specifications :

- Voltage rating: 125V AC / DC
- Current rating: 3A AC / DC
- Withstanding voltage: 1000V AC/minute
- Temperature range: -40°C~+105°C
- Insulation resistance: $\geq 1000M\Omega$
- Contact resistance: $\leq 10m\Omega$
- After environmental testing: $\leq 20m\Omega$

X2004 H- 02-N0

① ② ③ ④

- ① SeriesNumber
- ② Category : H-HSG
- ③ Row No.Pin No:xx-02-16P
- ④ Material:N0-PA66;



Poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	C		A	B	C
02	2.00	6.00	4.80	10	18.00	22.00	20.80
03	4.00	8.00	6.80	11	20.00	24.00	22.80
04	6.00	10.00	8.80	12	22.00	26.00	24.80
05	8.00	12.00	10.80	13	24.00	28.00	26.80
06	10.00	14.00	12.80	14	26.00	30.00	28.80
07	12.00	16.00	14.80	15	28.00	32.00	30.80
08	14.00	18.00	16.80	16	30.00	34.00	32.80
09	16.00	20.00	18.80				

X2004H-02-N0	PA66 UL 94V-0	X2004T	X2004W
PARY N0	Matrial	Suitable XKB Terminal	Suitable XKB Wafer

							DSND		DATE		SCALE: N/A	MODEL TYPE: 2.0mm Crimp Style Connectors						
Δx					ANGLAR	±5°	DWN		DATE		VIEW: 	PART NO.: X2004H-02-N0						
Δx					L ≤ 4	±0.2	CHKD		DATE		UNIT: mm/in	DWG NO.: X-X2004H-02-N0						
Δx					4<L ≤ 16	±0.3	APPD		DATE		SIZE: A4							
Δx					16<L ≤ 63	±0.4	XKB INDUSTRIAL PRECISION CO.,LIMITED						WEIGHT	SHEET	REVISION			
MARK	DESCRIPTION				DATE	REVISED							APPROVED	L > 63	±0.5	1.0g	1/1	A0
REVISIONS													UNSPECIFIED TOLERANCES					
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn																		

					ANGLAR	±5°
ΔX					L≤4	±0.2
ΔX					4<L≤16	±0.3
ΔX					16<L≤63	±0.4
MARK					L>63	±0.5
REVISIONS						UNSPECIFIED TOLERANCES
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn						