



	REVISIONS				
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.06.17	阿树




SS-12D06 L 5 R

Knob Type
L
G




H(mm)
2~12

Colour
Blank:Standard Black
R:Red



Typical Specifications

- 1.Rating:AC 125V 3A
- 2.Insulation Resistance:1,000M min
- 3.Dielectric strength:1,500V RMS
- 4.Operating Life: 10,000 cycles



SCHEMATIC

AuGLAR	$\pm 5^\circ$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:		MODEL TYPE:	SLIDE SWITCH
CHECKED		UNIT:	mm/in	PART NO.:	SS-12D06 L5R
APPROVED		SIZE:	A4	DWG NO.:	X-SS-12D06 L5R
PRECISION CO., LIMITED				SCALE	PAGE
				N/A	1/1
					REVISION
					A1