








REVISIONS				
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE
A1	N/A			2025.06.23
A2	N/A	A2X1		2025.09.04



Specifications()

- 1.Voltage rating():DC 30V
- 2.Current rating():100mA AC/DC
- 3.Withstanding voltage():≥250V AC/minute
- 4.Insulation resistance():≥100MΩ Min
- 5.Contact resistance():≤200mΩ Max
- 6.Mating cycles 10,000 cycles Min
- 7.Operating force 250±50gf
- 8.Tracel 2.30±0.20mm
- 8.Temperature range():-40 ~+85

PAPT NO	XKB7070-X-92
OPERATION	W:NO LOCK Z:LOCK

7	crochet hook	1	Sus	Natural
6	Spring	1	Sus	Natural
5	Reeds	1	Compound silver	Natural
4	Cover	1	PA66	White
3	Keystake	1	PA66	Blue
2	Terminal	1	Brass	Ag-Plating
1	Base	1	PA66	Black
ITEM	PAPT NAMF	QTY	MATERIAL	FINISHING/COLOR

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERAUCES	



DESIGN	
CHECKED	
APPROVED	

VIEW: UNIT: mm/in
SIZE: A4

MODEL TYPE:	KEY SWITCH
PART NO.:	XKB7070-X-92
DWG NO.:	