

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2024.12.24	阿树

Temperature range: -40℃--+125℃
温度范围: -40℃--+125℃

PART NO.:

K 828801 H-2x07-N0
① ② ③ ④ ⑤

- ①K:XKBTEK-Car Connector
②XKB Series No
③Category:H-Housing
④Row No.Pin No:2xXX-2x02~2x11 Pin
⑤Material:N0-PA66 UL94V-0 (Black)

Poles	Dimensions(mm)	
	A	B
2x02	11.00	5.00
2x03	16.00	10.00
2x04	21.00	15.00
2x05	26.00	20.00
2x07	36.00	30.00
2x09	46.00	40.00
2x11	56.00	50.00

K828801H-2x07-N0	PA66	K828801W	K828801T
PART NO	Material	Suitable XKB Wafer	Suitable XKB Terminal

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树
CHECKED	
APPROVED	

VIEW:	
UNIT:	mm/in
SIZE:	A4

MODEL TYPE:	5.00mm Automobile connector
PART NO.:	K828801H-2x07-N0
DWG NO.:	X-K828801H-2x07-N0

SCALE	PAGE	REVISION
N/A	1/1	A1