



REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.05.22	阿树



PART NO.:

X02 15 F I 7 BL 1
① ② ③ ④ ⑤ ⑥ ⑦



- ①Series NO.
②Row No.Pin No.XX-09;15;25;37
③Welding Board Angle :F-Female
④T: Tradutlional C: Car-pin
⑤Planting Catogtry: 1:1U' 2:2U' 3:3U' 4:5U'
5:15U' 6:30U' 7:AU5n
⑥Color:B-BLACK W-White BL-Blue
⑦1:TYPE-1; 2:TYPE-2; 5:TYPE-5; 7:TYPE-7

Specifications:

规格:

- 1.Voltage rating:250VAC/DC
额定电压: 250V AC/DC
 - 2.Current rating:1A AC/DC
额定电流: 1A AC/DC
 - 3.Withstanding voltage:500V AC/minute
耐受电压: ≥500V AC/分钟
 - 4.Temperature range: -55℃--+105℃
温度范围: -55℃--+105℃
 - 5.Insulation resistance:1000MΩMIN
绝缘电阻: ≥1000MΩ
 - 6.Contact resistance:30mΩMax
接触电阻: ≥30mΩ
- Material:
材料:
7.Rubber core:PBT UL94V-0
胶芯: PBT UL94V-0
8.The iron shell:SPCC Nivkel Plating/Tin Plating/Gold Plating
铁壳: SPCC,镀镍/镀锡/镀金
B、成品不能有弯针, R角不一致等不良。

NUMBER OF POSITIONS	DIMENSION			
	A±0.25	B±0.13	C±0.38	D±0.25
9	30.80	24.99	16.35	19.28
15	39.20	33.32	24.75	27.51
25	53.05	47.04	38.35	41.28
37	69.40	63.50	54.75	57.71



铆合方式	TYPE-1:铆合	TYPE-2:前铆实心螺母	TYPE-7:后铆鱼叉	TYPE-5:铆鱼叉锁螺丝
图示				

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:	MODEL TYPE: D-SUB
CHECKED		UNIT: mm/in	PART NO.: X0215FT7BL1
APPROVED		SIZE: A4	DWG NO.: X-X0215FT7BL1
		SCALE N/A	PAGE 1/1
			REVISION A1