









Recommended Panel Cut - Out
Thick:1.27mm Min/1.57mm Max

Specifications:

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating:5A AC/DC

额定电流: 5A AC/DC

Withstanding voltage:1000V AC/minute

耐受电压: 1000V AC/ 分钟

Temperature range:-40 °C -+105 °C

温度范围: -40℃ -+105℃

Insulation resistance:≥1000MΩ

绝缘电阻: ≥1000MΩ

Contact resistance:≤10mΩ

接触电阻: ≤10mΩ

X3025 H M - 2x02 WS - N0

① ② ③ ④ ⑤ ⑥

1.Series No

2.Category:H-HSG

3.Category:M-Male Housing

4.Row No.Pin No:XX-2x01~2x12P

5.Special No:WS-With Base

6.Material:N0-PA66 94V-0

Poles	Dimensions(mm)				Poles	Dimensions(mm)			
	A	B	C	D		A	B	C	D
2x01	/	/	/	/	2x07	39.80	18.00	28.46	37.10
2x02	24.60	3.00	13.46	22.10	2x08	42.80	21.00	31.46	40.10
2x03	27.70	6.00	16.46	25.10	2x09	45.80	24.00	34.46	43.10
2x04	30.70	9.00	19.46	28.10	2x10	48.80	27.00	37.46	46.10
2x05	33.80	12.00	22.46	31.10	2x11	51.80	30.00	40.46	49.10
2x06	36.80	15.00	25.46	34.10	2x12	54.80	33.00	43.46	52.10

X3025HM-2x02WS-N0	PA66	X3025W	X3025TF
PART N0	Material	Suitable XKB Wafer	Suitable XKB Terminal

					ANGLAR	±5°
Δx					L≤ 4	±0.2
Δx					4<L≤ 16	±0.3
Δx					16<L≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L> 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						

XKB

XKB INDUSTRIAL PRECISION CO.,LIMITED

DSND	SCALE: N/A	MODEL TYPE: 3.0mm Crimp Style Connector
DWN	VIEW:	PART NO.: X3025HM-2x02WS-N0
CHKD	UNIT: mm/in	DWG NO.: X-X3025HM-2x02WS-N0
APPD	SIZE: A4	WEIGHT
		SHEET
		REVISION
		1/1
		A0