

1

2


3

4


REVISIONS

REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2024.9.12	阿树


A





B



C



D



■ SPECIFICATIONS

- Voltage rating: 250V AC/DC
- Current rating: 3A AC/DC
- Withstanding Voltage: 1000V AC/minute
- Temperature range: -40°C ~ +125°C
- Insulation resistance: ≥ 1000MΩ
- Contact resistance: ≤ 10mΩ

PART NO.:

X2508 W V S-04-9T SW
① ② ③ ④ ⑤ ⑥ ⑦

- ① Series No
② Category: W-Wafer
③ Welding Board Angle: V-Stright 180°
④ Welding Way: S-SMT
⑤ Row No. Pin No: XX-02~15Pin
⑥ Material: 9T-PA9T 94V-0
⑦ Planting: SW-Matte Tin Plating

Poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	C		A	B	C
02	2.00	10.00	5.30	09	16.00	24.00	6.40
03	4.00	12.00		10	18.00	26.00	
04	6.00	14.00	6.40	11	20.00	28.00	
05	8.00	16.00		12	22.00	30.00	
06	10.00	18.00		13	24.00	32.00	
07	12.00	20.00		14	26.00	34.00	
08	14.00	22.00		15	28.00	36.00	

X2508WVS-04-9TSW	PA9T	Barss	X2508H
PART NO	Material	Material(Pin)	Suitable XKB Housing

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:	
CHECKED		UNIT:	mm/in
APPROVED		SIZE:	A4

MODEL TYPE: 2.50mm Crimp Style Connectors		
PART NO.: X2508WVS-04-9TSW		
DWG NO.: X-X2508WVS-04-9TSW		
SCALE	PAGE	REVISION
N/A	1/1	A1

www.helloxkb.com

www.helloxkb.cn

www.xk-dg.cn

XKB INDUSTRIAL PRECISION CO., LIMITED

1

2

3

4