

1


2

3


4

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.2.27	阿树


A



B



C



PCB LAYOUT

D

AuGLAR	$\pm 5^\circ$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED TOLERANCES	



XKB INDUSTRIAL PRECISION CO.,LIMITED

X1311WV-33J-C18D27	PA6T 94V-0	Brass	1U"Gold	X1311F
PART NO	Material	Material(Pin)	Finish(Pin)	Suitable XKB Female

DESIGN	阿树	VIEW: 	MODEL TYPE: 1.27mm BTB Connector		
CHECKED		UNIT: mm/in	PART NO.: X1311WV-33J-C18D27		
APPROVED		SIZE: A4	DWG NO.: X-X1311WV-33J-C18D27		
PRECISION CO., LIMITED			SCALE	PAGE	REVISION
			N/A	1/1	A1

规格 Specifications:

额定电压 Voltage rating:250VAC/DC.

额定电流 Current rating:1A AC/DC

耐电压 Withstanding voltage:300V AC/minute

温度区间 Temperature range:-40℃to+105℃

绝缘电阻 Insulation resistance: $\geq 500M\Omega$ Min接触电阻 Contact resistance: $\leq 20M\Omega$ Max

材料 Material: PA6T 94V-0

镀层 Plating Category: 1U"Gold

波峰焊温度 Wave soldering temperature:255 $\pm$ 5℃,10s

PART NO.:

X1311 W V-33 J-C18 D27
① ② ③ ④ ⑤ ⑥ ⑦

①Series No

②Category:W-Water


③Welding Board Angle:V-Straight 180°

④Row No -Pin No:XX-01P-40P

⑤Plastic height: J=1.0mm

⑥Plastic length:C=2.7mm

⑦Plastic length:D=1.8mm



www.helloxkb.com

www.helloxkb.cn

www.xk-dg.cn

1

2

3

4