

Specifications:

规格:

Voltage rating:30V AC/DC

额定电压: 30V AC/DC

Current rating: 0.2A AC/DC

额定电流: 0.2A AC/DC

Withstanding voltage:200V AC/minute

耐压电压: 200V AC/分钟

Temperature range:-25℃~+85℃

温度范围: $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$

Insulation resistance: $\geq 100\text{M}\Omega$

绝缘电阻: $\geq 100\text{M}\Omega$

Contact resistance: $\leq 30\text{m}\Omega$

接触电阻: $\leq 30\text{m}\Omega$

X0600 W R S - 08 - LP V01 HF

① ②③④ ⑤ ⑥ ⑦ ⑧

①Series No.

②Category: W-wafer


③Welding Board Angle: R-90°

④Row No.-Pin No.: XX-Single row

⑤Material: LP-LCP 94V-0

⑥Planting Category : V01-All Gold Flash

⑦ Plug the Pin & Special NO.:HF-Halogen Free



Recommended P.C.B Layout

General Tolerance ± 0.05

Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
2	0.60	3.00	12	6.60	9.00
3	1.20	3.60	13	7.20	9.60
4	1.80	4.20	14	7.80	10.20
5	2.40	4.80	15	8.40	10.80
6	3.00	5.40	16	9.00	11.40
7	3.60	6.00	17	9.60	12.00
8	4.20	6.60	18	10.20	12.60
9	4.80	7.20	19	10.80	13.20
10	5.40	7.80	20	11.40	13.80
11	6.00	8.40	22	12.60	15.00

X0600WRS-08-LP01HF	LCP	Phosphor Bronze	X0600WRS
PART NO	Material	Material(Pin)	Suitable XKB Housing

					ANGLAR	±5°
Δx					L ≤ 4	±0.2
Δx					4 < L ≤ 16	±0.3
Δx					16 < L ≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L > 63	±0.5

REVISIONS

www.helloxkb.com www.helloxkb.cn www.xk-dg.cn

UNSPECIFIED TOLERANCES

XKLE

XKB INDUSTRIAL PRECISION CO.,LIMITED

DSND		SCALE: N/A	MODEL TYPE: 0.6mm Crimp Style Connector		
DWN		VIEW: 	PART NO.: X0600WRS-08-LPV01HF		
CHKD		UNIT: mm/in	DWG NO.: X-X0600WRS-08-LPV01HF		
APPD		SIZE: A4			
L. PRECISION CO., LIMITED			WEIGHT	SHEET	REVISION
				1/1	A0