





SECTION A-A



NOTE :

1.MATERIAL 材料:

HOUSING 胶壳: LCP.UL94V-0

CONTACT 端子:C5191

SHELL 外壳:BRASS

2.FINISH 电镀:

CONTACT 端子: C5191, GOLD OVER NICKEL

SHELL 外壳: BRASS, GOLD FLASH ALL PLATING.

3. Electrical parameters 电气参数

Contact Current Rating 触点电流额定值: 0.5A Min

Voltage Rating 额定电压: 40V AC(RMS)

Operating temperature 工作温度: $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$

4.Durability 耐用性: 10000 cycles

A72-16J3-555G1

1:AU 1U"

5:AU 15U"

6:AU 30U"

					ANGLAR	±5°
Δx					L≤ 4	±0.2
Δx					4<L≤ 16	±0.3
Δx					16<L≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L> 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dq.cn						



XKB INDUSTRIAL PRECISION CO.,LIMITED

DSND		SCALE: N/A	MODEL TYPE: HDMI CONNECTOR		
DWN		VIEW: 	PART NO.: A72-16J3-555G1		
CHKD		UNIT: mm/in	DWG NO.: A72-16J3-555G1		
APPD		SIZE: A4			
PRECISION CO.,LIMITED			WEIGHT	SHEET 1/1	REVISION A0