





REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.2.24	阿树



P.C.B LAYOUT



Specifications:
规格:
Voltage rating:250V AC/DC
额定电压: 250V AC/DC
Current rating:1A AC/DC
额定电流: 1A AC/DC
Withstanding voltage:300V AC/minute
耐受电压: 300V AC/分钟
Temperature range:-40℃--+105℃
温度范围: -40℃--+105℃
Insulation resistance:≥500MΩ
绝缘电阻: ≥500MΩ
Contact resistance:≤20mΩ
接触电阻: ≤20mΩ
Material:PA6T UL94V-0
材质: PA6T UL94V-0
Plating Category:1U"Gold
镀层: 1U"Gold
Reflow soldring temperature:260±5℃, 10S
回流焊温度: 260±5℃, 10S

PART NO.:
X1321 W V S-2x02 J-C40 D53
① ② ③ ④ ⑤ ⑥ ⑦ ⑧

- ①Series No
②Category:W-Wafer
③Welding Board Angle:V-Stright 180°
④Welding Way:S-SMT
⑤Row No.Pin No:2xXX-2x01~2x40Pin
⑥Plastic Height:J=1.0mm
⑦Pin Length:C=4.0mm
⑧Pin Length:D=5.3mm

X1321WVS-2x02J-C40D53		PA6T	Brass	X1321F
PART NO		Material	Material(Pin)	Suitable XKB Female
DESIGN	阿树	VIEW:	MODEL TYPE: 1.27mm BTB Connector	
CHECKED		UNIT: mm/in	PART NO.: X1321WVS-2x02J-C40D53	
APPROVED		SIZE: A4	DWG NO.: X-X1321WVS-2x02J-C40D53	
			SCALE	PAGE
			N/A	1/1
			REVISION	A1

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



XKB INDUSTRIAL PRECISION CO.,LIMITED