






Specifications:

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating:1A AC/DC

额定电流: 1A AC/DC

Withstanding voltage:500V AC/minute

耐受电压: 500V AC/分钟

Temperature range:-40℃--+105℃

温度范围: -40℃--+105℃

Insulation resistance: 1000MΩ min

绝缘电阻: 1000MΩ Min

Contact resistance:20mΩ Max

接触电阻: 20mΩ Max

X2001	H2	-2x20	-PT	V01
①	②	③	④	⑤

1.Series No

2.Category:H2-three-piece

3.Row No.Pin No:2xXX-2x03-2x30P

4.Material:PT-PBT Glass Fiber UL94V-0

5.Plating:V01-Gold Flash

Poles	DIM A	DIM B
2x03	11.20	4.00
2x04	13.20	6.00
2x05	15.20	8.00
2x06	17.20	10.00
2x07	19.20	12.00
2x08	21.20	14.00
2x09	23.20	16.00
2x10	25.20	18.00
2x11	27.20	20.00
2x12	29.20	22.00
2x13	31.20	24.00
2x14	33.20	26.00
2x15	35.20	28.00
2x17	39.20	32.00
2x18	41.20	34.00
2x20	45.20	38.00
2x22	49.20	42.00
2x25	55.20	48.00
2x30	65.20	58.00

X2001H2-2x20-PTV01	PBT Glass Fiber	Brass	X2001W-A/X2001W-C
PART NO	Material	Material(Pin)	Suitable XKB Wafer

DSND	SCALE: N/A	MODEL TYPE:
DWN	VIEW:	2.0mm IDC Connector
CHKD	UNIT: mm/in	PART NO.:
APPD	SIZE: A4	X2001H2-2x20-PTV01
		DWG NO.:
		X-X2001H2-2x20-PTV01

					ANGLAR	±5°
ΔX					L≤ 4	±0.2
ΔX					4<L≤ 16	±0.3
ΔX					16<L≤ 63	±0.4
MARK					L> 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						

XKB

XKB INDUSTRIAL PRECISION CO.,LIMITED

WEIGHT	SHEET	REVISION
	1/1	A0