








P.C.B Layout
XKB Connectivity



XKB Connectivity

■ 规格 Specifications:

- 额定电压 Voltage rating:150 V AC/DC
- 额定电流 Current rating:1A AC/DC
- 耐电压 Withstanding voltage:1000 V AC/minute
- 温度区间 Temperature range:-25℃~+105℃
- 绝缘电阻 Insulation resistance:>1000MΩ
- 接触电阻 Contact resistance:<20mΩ

XKB Connectivity

X3000W F -02-LPSW
① ② ③ ④ ⑤ ⑥

- ① Series No
- ② Category:W-WAFER
- ③ Welding Board Angle:F-Female
- ④ Row No.-Pin No.: XX-Single Row
- ⑤ Material:LP-LCP 94V-0
- ⑥ Plating Category: SW-Fog Tin plating

XKB Connectivity

X3000WF-02-LPSW	LCP UL 94V-0	Phosphor Bronze	Tin-Plated	Brass	Tin-Plated
PART NO	Material	Material(Pin)	Finish(Pin)	Material (Solder Tab)	Finish (Solder Tab)

							DSND		DATE		SCALE: N/A	MODEL TYPE: X3000WF-02-LPSW			
					ANGLAR	±5°	DWN		DATE		VIEW: 	PART NO.: 4.00mm BTB Style Connectors			
Δx					L ≤ 4	±0.2	CHKD		DATE		UNIT: mm/in	DWG NO.: X3000WF-02-LPSW			
Δx					4<L ≤ 16	±0.3									
Δx					16<L ≤ 63	±0.4	APPD		DATE		SIZE: A4				
MARK	DESCRIPTION			DATE	REVISED	APPROVED									
REVISIONS							UNSPECIFIED TOLERANCES								
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn							XKB INDUSTRIAL PRECISION CO.,LIMITED						WEIGHT	SHEET	REVISION
													1.0g	1/1	A0