



| REVISIONS |         |          |                 |            |        |
|-----------|---------|----------|-----------------|------------|--------|
| REV.      | ECN NO. | LOCATION | DESCRIPTION     | DATE       | DESIGN |
| A0        | N/A     |          | INITIAL RELEASE | /          | /      |
| A1        | N/A     |          | 图面升级整理图面        | 2025.05.22 | 阿树     |



Specifications:  
规格:  
1.Voltage rating:250VAC/DC  
额定电压: 250V AC/DC  
2.Current rating:1A AC/DC  
额定电流: 1A AC/DC  
3.Withstanding voltage:500V AC/minute  
耐受电压: ≥500V AC/分钟  
4.Temperature range:-40℃-+105℃  
温度范围: -40℃-+105℃  
5.Insulation resistance:1000MQMIN  
绝缘电阻: ≥1000MQ  
6.Contact resistance:20mΩMax  
接触电阻: ≥20mΩ  
Material:  
材料:  
7.Rubber core:PBT UL94V-0  
胶芯: PBT UL94V-0  
8.The iron shell:SPCC Nivkel Plating/Tin Plating  
铁壳: SPCC,镀镍/镀锡  
B. 成品不能有弯针, R角不一致等不良。



PART NO.:

X07 37 W I Z B 1  
① ② ③ ④ ⑤ ⑥ ⑦

- ①Series NO.  
②Row No.Pin No.XX-09;15;25;37  
③Welding Board Angle :W-Male  
④T: Tradutlional C: Car-pin  
⑤Planting Categorty: 1:1U' 2:2U' 3:3U' 4:5U'  
5:15U' 6:30U' 7:AUsn  
⑥Color:B-BLACK W-White BL-Blue  
⑦1:TYPE-1;

| NUMBER OF POSITIONS | DIMENSION |        |        |        |        |
|---------------------|-----------|--------|--------|--------|--------|
|                     | A±0.40    | B±0.30 | C±0.30 | D±0.65 | E±0.25 |
| 9                   | 30.80     | 25.00  | 16.35  | 11.08  | 10.16  |
| 15                  | 39.14     | 33.30  | 24.75  | 19.39  | 17.78  |
| 25                  | 53.05     | 47.04  | 38.35  | 33.24  | 30.38  |
| 37                  | 69.32     | 63.50  | 54.75  | 49.86  | 45.72  |

|            |       |       |
|------------|-------|-------|
| X07XXWXXX1 | XDBLS | XDBLM |
| PART NO    | SCREW | NUT   |



|                        |       |
|------------------------|-------|
| AuGLAR                 | ±5°   |
| X.                     | ±0.40 |
| X.x                    | ±0.30 |
| X.xx                   | ±0.20 |
| X.xxx                  | ±0.15 |
| UNSPECIFIED TOLERANCES |       |



|                       |    |       |                                                                                       |                          |      |          |
|-----------------------|----|-------|---------------------------------------------------------------------------------------|--------------------------|------|----------|
| DESIGN                | 阿树 | VIEW: |  | MODEL TYPE:<br>D-SUB     |      |          |
| CHECKED               |    | UNIT: | mm/in                                                                                 | PART NO.:<br>X0737WT7B1  |      |          |
| APPROVED              |    | SIZE: | A4                                                                                    | DWG NO.:<br>X-X0737WT7B1 |      |          |
| PRECISION CO.,LIMITED |    |       |                                                                                       | SCALE                    | PAGE | REVISION |
|                       |    |       |                                                                                       | N/A                      | 1/1  | A1       |