





■ Specifications :

- Voltage rating: 250V AC / DC
- Current rating: 3A AC / DC
- Withstanding voltage: 800V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance: $\geq 1000M\Omega$
- Contact resistance: $\leq 10m\Omega$
- After environmental testing : $\leq 20m\Omega$

X2581 W V-05 - N0 SN

① ② ③ ④ ⑤ ⑥

- ① Series No.
- ② Category : W-WAFER
- ③ Wedging Board Angle : V-Stright 180°
- ④ Row No.-Pin No.: XX-02P~15P
- ⑤ Material : N0-PA66;46-PA46 94V-0
- ⑥ Plating Category: Sn-Bright Tin Plating

Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
02	2.50	7.50	12	27.50	32.50
03	5.00	10.00	13	30.00	35.00
04	7.50	12.50	14	32.50	37.50
05	10.00	15.00	15	35.00	40.00
06	12.50	17.50			
07	15.00	20.00			
08	17.50	22.50			
09	20.00	25.00			
10	22.50	27.50			
11	25.00	30.00			

							DSND		DATE		SCALE: N/A	MODEL TYPE: 2.5mm Crimp Style Connectors		
ΔX					ANGLAR	±5°	DWN		DATE		VIEW: 	PART NO.: X2581WV-05-N0SN		
ΔX					4<L≤16	±0.3	CHKD		DATE		UNIT: mm/in	DWG NO.: X-X2581WV-05-N0SN		
ΔX					16<L≤63	±0.4	APPD		DATE		SIZE: A4			
MARK	DESCRIPTION			DATE	REVISED	APPROVED						L>63	±0.5	
REVISIONS							UNSPECIFIED TOLERANCES					XKB INDUSTRIAL PRECISION CO.,LIMITED		
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn												WEIGHT 1.0g	SHEET 1/1	REVISION A0