





由 AUTODESK 学生版生成



■ Specifications :

- Voltage rating: 250V AC / DC
- Current rating: 5A AC / DC
- Withstanding voltage: 1000V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance: ≥1000M Ω
- Contact resistance: ≤10mΩ
- After environmental testing : ≤20mΩ
- Mark "*"Indicate Dimensions Need To Controlled In Emphasis

P.C.B. LAYOUT



X3025 W V S- 04 C-LPSW

01 02 03 04 05 06 07 08 09

01 Series No.

02 Category :

W-wa fer

03 Welding Board Angle:

V-180°

04 Welding Way:

S-SMT

05 Row No.-Pin No.

XX-Single row

06 Special NO.

C-The ha fPoon

07 Material:

LP-LCP 94V-0 66-PA66 94V-0

08 Planting Category:

V**All Gold-Plated

G**Gold-Plated Contact

*01-Gold Flash ; *02-2U" ; *03-3U" ; *05-5U"

*10-10U" ; *15-15U" ; *30-30U" ; *50-50U"

SN-Bright tin plating 70U"

SN1-Bright tin plating 120U"Min. ;

SW-Fog Tin plating

09 Color:

Blank-natural color

Poles	Dimensions (mm)		
	A	B	C
02	6.85	3.00	7.30
03	9.85	6.00	10.30
04	12.85	9.00	13.30
05	15.85	12.00	16.30
06	18.85	15.00	19.30
07	21.85	18.00	22.30
08	24.85	21.00	25.30
09	27.85	24.00	28.30
10	30.85	27.00	31.30
11	33.85	30.00	34.30
12	36.85	33.00	37.30

X3025 WVS-04C-LPSW	LCP UL 94V-0	Brass	Tin Plating Fog	Brass	Tin-Plated	X3025H
X3025WVS-04C-66SN	PA66 UL 94V-0	Brass	Tin-Plated	Brass	Tin-Plated	X3025H
PART NO	Material	Material(pin)	Finish(Pin)	Material (Solder Tabs)	Finish (Solder Tabs)	Mates With XKB Housing

							DSND		DATE		SCALE: N/A	MODEL TYPE:
							DWN		DATE		VIEW:	3.00 mm Crimp Style Connectors
							CHKD		DATE		UNIT: mm/in	PART NO.:
							APPD		DATE		SIZE: A4	DWG NO.:
												X-X3025WVS-04C-LPSW
												WEIGHT
												1.0g
												SHEET
												1/1
												REVISION
												A0

REVISIONS

UNSPECIFIED TOLERANCES

www.helloxkb.com

由 AUTODESK 学生版生成

■ KXB INDUSTRIAL PRECISION CO.,LIMITED