

Specifications:

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating:3A AC/DC

额定电流: 3A AC/DC

Withstanding voltage:1000V AC/minute

耐受电压: 1000V AC/分钟

Temperature range:-25℃~+85℃

温度范围: -25℃~+85℃

Insulation resistance: 1000MΩ min

绝缘电阻: 1000MΩ Min





Contact resistance:20mΩ Max

接触电阻: 20mΩ Max

X8821 W V-05 A-N0 SN
① ② ③ ④ ⑤ ⑥ ⑦

- 1.Series No
2.Category:W-Wafer
3.Welding Board Angle:V-Straight 180°
4..Row No-Pin No:XX-03P~20P
5.TYPE:A
6.Material:N0-Nylon66 UL94V-0
7.Plating Category:SN-Bright Tin Plating

Poles	Dimensions(mm)	
	A	B
03	5.00	10.00
04	7.50	12.50
05	10.00	15.00
06	12.50	17.50
07	15.00	20.00
08	17.50	22.50
09	20	25.00
10	22.50	27.50
11	25.00	30.00
12	27.50	32.50
20	47.50	52.50



PCB LAYOUT

X8821WV-05A-N0SN	Nylon66	Phosphor bronze	X8821H	X8821T
PART NO	Material	Material(PIN)	Suitable XKB Housing	Suitable XKB Terminal

					ANGLAR	±5°
ΔX					L≤ 4	±0.2
ΔX					4<L≤ 16	±0.3
ΔX					16<L≤ 63	±0.4
MARK					L> 63	±0.5

REVISIONS				UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn					



XKB INDUSTRIAL PRECISION CO.,LIMITED

DSND		SCALE: N/A	MODEL TYPE: 2.5 mm BTB Style Connector
DWN		VIEW: 	PART NO.: X8821WV-05A-N0SN
CHKD		UNIT: mm/in	DWG NO.: X-X8821WV-05A-N0SN
APPD		SIZE: A4	
PRECISION CO.,LIMITED			WEIGHT
			SHEET
			1/1
			REVISION
			A0