



	REVISIONS				
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.06.17	阿树




SS-12D10

Knob Type
L
G




H(mm)
2~12

Colour
Blank:Standard Black
R:Red



Typical Specifications

- 1.Rating:AC 125V 3A
- 2.Insulation Resistance:1,000M min
- 3.Dielectric strength:1,500V RMS
- 4.Operating Life: 10,000 cycles



5	Terminal	3	Copper Alloy	silver plated
4	Contact	1	Copper Alloy	silver plated
3	Housing	1	Stainless Steel	
2	Slide Handle	1	Nylon	
1	Case	1	Diallyl Phthalate (DAP)	
ITEM	PAPT NAME	QTY	MATERIAL	FINISHING

AuGLAR	$\pm 5^\circ$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED TOLERANCES	

XKB 星城
Connection

DESIGN	阿树	VIEW:		MODEL TYPE:	SLIDE SWITCH	
CHECKED		UNIT:	mm/in	PART NO.:	SS-12D10G6	
APPROVED		SIZE:	A4	DWG NO.:	X-SS-12D10G6	
PRECISION CO., LIMITED				SCALE	PAGE	REVISION
				N/A	1/1	A1