



## Specifications.

- Voltage rating: 250V AC/DC
- Current rating: 7A AC/DC
- Withstanding voltage: 1500V AC/minute
- Temperature range: -25°C ~ +85°C
- Insulation resistance: 1000mΩ Min
- Contact resistance: 20mΩ Max
- Material: Nylon66 UL94V-0

X8475 W V -07- N0 SN  
① ② ③ ④ ⑤ ⑥

- ① Series No.
- ② Category : W-WAFER
- ③ Wedging Board Angle : V-Straight 180°
- ④ Row No. Pin No. XX-02-08
- ⑤ Material: N0-Nylon UL94V-0
- ⑥ Planting Category: SN-Bright Tin plating

| Poles | Dimensions (mm) |       |
|-------|-----------------|-------|
|       | A               | B     |
| 2     | 7.50            | 15.20 |
| 3     | 12.50           | 20.20 |
| 4     | 17.50           | 25.20 |
| 5     | 22.50           | 30.20 |
| 6     | 27.50           | 35.20 |
| 7     | 32.50           | 40.20 |
| 8     | 37.50           | 45.20 |

|                 |                  |               |             |                      |
|-----------------|------------------|---------------|-------------|----------------------|
| X8475WV-07-N0SN | Nylon66 UL 94V-0 | Brass         | Tin-Plated  | X8475H               |
| PART NO         | Material         | Material(Pin) | Finish(Pin) | Suitable XKB Housing |

| MARK | DESCRIPTION | DATE | REVISED | APPROVED | UNSPECIFIED TOLERANCES |
|------|-------------|------|---------|----------|------------------------|
| ΔX   |             |      |         |          | ANGULAR                |
| ΔX   |             |      |         |          | L ≤ 4                  |
| ΔX   |             |      |         |          | 4 < L ≤ 16             |
| ΔX   |             |      |         |          | 16 < L ≤ 63            |
| MARK |             |      |         |          | L > 63                 |

XKLB

|      |  |             |                               |
|------|--|-------------|-------------------------------|
| DSND |  | SCALE: N/A  | MODEL TYPE:                   |
| DWN  |  | VIEW:       | 7.50mm Crimp Style Connectors |
| CHKD |  | UNIT: mm/in | PART NO.:                     |
| APPD |  | SIZE: A4    | X847WV-07-N0SN                |
|      |  |             | DWG NO.:                      |
|      |  |             | X-X8475WV-07-N0SN             |
|      |  |             | WEIGHT                        |
|      |  |             | SHEET                         |
|      |  |             | REVISION                      |
|      |  |             | 1/1                           |
|      |  |             | A0                            |

XKB INDUSTRIAL PRECISION CO., LIMITED

www.helloxkb.com www.helloxkb.cn www.xk-dg.cn