




PCB Board Layout

Specifications:
规格:
Voltage rating:600V AC/DC
额定电压: 600V AC/DC
Current rating:23A AC/DC
额定电流: 23A AC/DC
Withstanding voltage:2200V AC/minute
耐受电压: 2200V AC/分钟
Temperature range:-40℃~+105℃
温度范围: -40℃~+105℃
Insulation resistance:1000MΩ min
绝缘电阻: 1000MΩ Min
Contact resistance:10mΩ Max
接触电阻: 10mΩ Max

X5701 W V - 04 -LP SW
① ② ③ ④ ⑤ ⑥

- 1.Series No
- 2.Category:W-Wafer
- 3.Welding Board Angle:V-Straight 180°
- 4.Row No.Pin No:XX-02~12P ;N=4~12P
- 5.Material:LP-LCP UL94V-0 Black
Pin:High Contactivity Copper Alloy
- 6.Plating:SW-Matte Tin Plating

Circuits	2	N
DIM .A	5.70	5.7xN-5.7
DIM .B	12.05	5.7xN+0.65
DIM .C	/	5.7x(N-2)

X5701WV-04-LPSW	LCP	High Contactivity Copper Alloy	X5701H
PART NO	Material	Material(Pin)	Suitable XKB Housing

DSND		SCALE: N/A	MODEL TYPE: 5.7mm Crimp Style Connector
DWN		VIEW:	PART NO.: X5701WV-04-LPSW
CHKD		UNIT: mm/in	DWG NO.: X-X5701WV-04-LPSW
APPD		SIZE: A4	

ΔX	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
ΔX					
ΔX					
MARK					
REVISIONS					
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn					

XKLB

XKB INDUSTRIAL PRECISION CO.,LIMITED

WEIGHT	SHEET	REVISION
	1/1	A0