

Code-x	H
A	4.30
B	4.50
C	5.00
D	5.50
E	6.00
F	6.50
G	7.00
H	7.50
I	8.00
J	8.50
K	9.00
L	9.50
M	10.00
N	10.50

SPECIFICATION
Contact Rating: 50mA, 12V DC
Contact Resistance: 100mΩ max
Insulation Resistance: 100MΩ min. 500V DC
Dielectric Strength: 250V AC/1minute
Travel: 0.25mm
Operating Temp: -30℃~+85℃
Storage Temp: -30℃~+80℃

PAPT NO	TC-1103-C-A
Operating Force	B:160gf C:260gf
Height	Code-x

⑤	Terminal	4	Brass .030t)	Plating silvering
④	Contact	1	F.ag/SUS	Natural
③	Base	1	PA46	
②	Cover	1	Spcc	Plating Nickel
①	Keystone	1	PA46	
ITEM	PAPT NAMF	QTY	MATERIAL	FINISHING

AuGLAR	$\pm 5^\circ$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED	TOLERAuCES

XKB 星城
Connection

DESIGN	阿树	VIEW: 	MODEL TYPE: TACT SWITCH		
CHECKED		UNIT: mm/in	PART NO.: TC-1103-C-A		
APPROVED		SIZE: A4	DWG NO.: TC-1103-C-A		
CISION CO.,LIMITED			SCALE	PAGE	REVISION
			N/A	1/1	A1

