










X1004H-XXA-N0HF
02-05Pin



X1004H-XXA-N0HF
06-15Pin



Specifications:

规格:

Voltage rating:100V AC/DC

额定电压: 100V AC/DC

Current rating:1A AC/DC

额定电流: 1A AC/DC

Withstanding voltage:300V AC/minute

耐受电压: 300V AC/分钟

Temperature range:-40℃-+105℃

温度范围: -40℃-+105℃

Insulation resistance:≥100MΩ

绝缘电阻: ≥100MΩ

Contact resistance:≤20mΩ

接触电阻: ≤20mΩ

X1004 H - 10 A - N0 HF
① ② ③ ④ ⑤ ⑥

1.Series No

2.Category:H-Housing

3.Row No.Pin No:XX-02-15 Pin

4.Special No:A-Inner Lock

5.Material:N0-PA66 UL94V-0

6.HF-Halogen Free

Poles	Dimensions(mm)		
	A	B	C
02	3.70	1.00	2.40
03	4.70	2.00	3.40
04	5.70	3.00	4.40
05	6.70	4.00	5.40
06	7.70	5.00	6.40
07	8.70	6.00	7.40
08	9.70	7.00	8.40
09	10.70	8.00	9.40
10	11.70	9.00	10.40
11	12.70	10.00	11.40
12	13.70	11.00	12.40
13	14.70	12.00	13.40
14	15.70	13.00	14.40
15	16.70	14.00	15.40

X1004H-10A-N0HF	PA66	X1004W-A	X1004T
PART N0	Material	Suitable XKB Wafer	Suitable XKB Terminal

DSND	SCALE: N/A	MODEL TYPE: 1.0mm Crimp Style Connector
DWN	VIEW:	PART NO.: X1004H-10A-N0HF
CHKD	UNIT: mm/in	DWG NO.: X-X1004H-10A-N0HF
APPD	SIZE: A4	

XKB

XKB INDUSTRIAL PRECISION CO.,LIMITED

					ANGLAR	±5°
Δx					L≤ 4	±0.2
Δx					4<L≤ 16	±0.3
Δx					16<L≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L> 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						

WEIGHT	SHEET	REVISION
	1/1	A0