





PCB LAYOUT

2PIN

技术要求:

- 1) 材质:见附表;
- 2) 电镀:见附表;
- 3) 塑件表面平整、光洁、无毛刺、气泡、烧焦、变形、浇口无拉伤、多料或缺料等不良现象;
- 4) 端子表面无氧化、电镀不良等现象。

| GENERAL TOLERANCES |       |        |        |
|--------------------|-------|--------|--------|
| DIM                | TOL   | DIM    | DEG    |
| X.                 |       | X°.    | ±3.00° |
| X.X                | ±0.35 | X.X°   | ±2.00° |
| X.XX               | ±0.25 | X.XX°  | ±1.00° |
| X.XXX              | ±0.15 | X.XXX° |        |

| REV. | EC# | DESCRIPTION | DATE DRAWN | CHECK | APPROVED |
|------|-----|-------------|------------|-------|----------|
| 1.00 |     | 初版发行        | 2020-8-28  |       |          |
|      |     |             |            |       |          |
|      |     |             |            |       |          |

|                |      |       |       |
|----------------|------|-------|-------|
| 15P            | 40   | 38.6  | 35    |
| 14P            | 37.5 | 36.1  | 32.5  |
| 13P            | 35   | 33.6  | 30    |
| 12P            | 32.5 | 31.1  | 27.5  |
| 11P            | 30   | 28.6  | 25    |
| 10P            | 27.5 | 26.1  | 22.5  |
| 9P             | 25   | 23.6  | 20    |
| 8P             | 22.5 | 21.1  | 17.5  |
| 7P             | 20   | 18.6  | 15    |
| 6P             | 17.5 | 16.1  | 12.5  |
| 5P             | 15   | 13.6  | 10    |
| 4P             | 12.5 | 11.1  | 7.5   |
| 3P             | 10   | 8.6   | 5     |
| 2P             | 7.5  | 6.1   | 2.5   |
| NUMBER OF PINS |      | DIM.A | DIM.B |
|                |      | DIM.C |       |

适用基板厚度: 1.6mm  
温度范围: -25℃~85℃  
额定电压: 250V AC/DC  
额定电流: 3A  
接触电阻: ≤0.02Ω  
绝缘电阻: ≥1000MΩ  
耐 压: 1000V AC/minute

|     |         |       |                          |
|-----|---------|-------|--------------------------|
| 2   | PIN     | n PCS | 材质:黄铜,电镀:镀亮锡             |
| 1   | Housing | 1 PCS | 材质:PA66 (UL94V-0), 颜色:白色 |
| NO. | NAME    | Q'TY  | DESCRIPTION              |



深圳市韩下电子有限公司

DRAW : 黄彬2020-8-28

DESIGN: 张伟2020-8-28

APPROVED 罗小春2020-8-28

CUSTOMER DRAWING

TITLE: 针座

SERIES: XH2.5 SERIES

P/N:

REV. 1.00

SCALE N/A

DRAW NAME: HX-XH2. 54-3PWZ-WG

DRAW NO.

UNIT: mm

SHEET: 1/1





深圳市韩下电子有限公司  
Shenzhen Hanxia Electronic Co., Ltd  
Tel: 0755-23086569

## 承 认 书

### SPECIFICATION FOR APPROVAL

产 品 编 码  
Material code:

\_\_\_\_\_

产品名称 Project:

针座

\_\_\_\_\_

规格型号 Part No:

HX-XH2. 54-3PWZ-WG

\_\_\_\_\_

#### 贵公司承认印 Approval signatures

| 料 号/Part No. | 签 章/Signatures |
|--------------|----------------|
|              |                |

日期 Date:

|             |     |                                                                                      |
|-------------|-----|--------------------------------------------------------------------------------------|
| 拟制/Drawn    | 黄彬  |  |
| 审核/Check    | 张伟  |                                                                                      |
| 批准/Approved | 罗小春 |                                                                                      |