



P.C.B LAYOUT

Specifications:

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating:1A AC/DC

额定电流: 1A AC/DC

Withstanding voltage:300V AC/minute

耐受电压: 300V AC/分钟

Temperature range:-40℃-+105℃

温度范围: -40℃-+105℃

Insulation resistance:≥500MΩ

绝缘电阻: ≥500MΩ

Contact resistance:≤20mΩ

接触电阻: ≤20mΩ

Material:PA6T UL94V-0

材质: PA6T UL94V-0

Plating Category:1U"Gold

镀层: 1U"Gold

Wave soldering temperature:255±5℃, 10S

波峰焊温度: 255±5℃, 10S

X1321 F V - 2x04 - C43 D24
① ② ③ ④ ⑤ ⑥

- 1.Series No
- 2.Category:F-Female
- 3.Welding Board Angle:V-Straight 180°
- 4.Row No.Pin No:2xXX-2x01~2x40P
- 5.Plastic Height:C=4.3mm
- 6.Pin Length:D=2.4mm

X1321FV-2x04-C43D24	PA6T	Brass	X1321W
PART NO	Material	Material(Pin)	Suitable XKB Wafer

MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
ΔX					ANGULAR ±5°
ΔX					L ≤ 4 ±0.2
ΔX					4 < L ≤ 16 ±0.3
ΔX					16 < L ≤ 63 ±0.4
ΔX					L > 63 ±0.5
REVISIONS					
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn					

XKLB

XKB INDUSTRIAL PRECISION CO.,LIMITED

DSND	SCALE: N/A	MODEL TYPE:
DWN	VIEW:	1.27mm BTB Connector
CHKD	UNIT: mm/in	PART NO.: X1321FV-2x04-C43D24
APPD	SIZE: A4	DWG NO.: X-X1321FV-2x04-C43D24
		WEIGHT
		SHEET 1/1
		REVISION A0