






R1



R2



R1



R2

P.C.B LAYOUT

## Specifications:

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating:1A AC/DC

额定电流: 1A AC/DC

Withstanding voltage:300V AC/minute

耐受电压: 300V AC/分钟

Temperature range:-40℃~+105℃

温度范围: -40℃~+105℃

Insulation resistance:≥500MΩ

绝缘电阻: ≥500MΩ

Contact resistance:≤20mΩ

接触电阻: ≤20mΩ

Material:PA6T UL94V-0

材质: PA6T UL94V-0

Plating Category:1U"Gold

镀层: 1U"Gold

Reflow soldering temperature:260±5℃, 10S

回流焊温度: 260±5℃, 10S

X1311 W V S - 11 J - C40 D42 R1  
① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

1.Series No.

2.Category:W-Water

3.Welding Board Angle:V-Stright 180°

4.Welding Way S-SMT

5.Row No -Pin No:XX Pin

6.Plastic height:J=1.0mm

7.Pin length: C=4.0mm

8.Pin length:D=4.2mm

9.Type:X-R1;R2

|                       |          |               |                     |
|-----------------------|----------|---------------|---------------------|
| X1311WVS-11J-C40D42R1 | PA6T     | Brass         | X1311F              |
| PART NO               | Material | Material(Pin) | Suitable XKB Female |

|                         |      |  |                                                                                             |                                     |              |                |
|-------------------------|------|--|---------------------------------------------------------------------------------------------|-------------------------------------|--------------|----------------|
| }                       | DSND |  | SCALE: N/A                                                                                  | MODEL TYPE:<br>1.27mm BTB Connector |              |                |
|                         | DWN  |  | VIEW:  | PART NO.:<br>X1311WVS-11J-C40D42R1  |              |                |
|                         | CHKD |  | UNIT: mm/in                                                                                 | DWG NO.:<br>X-X1311WVS-11J-C40D42R1 |              |                |
|                         | APPD |  | SIZE: A4                                                                                    |                                     |              |                |
| L PRECISION CO.,LIMITED |      |  |                                                                                             | WEIGHT                              | SHEET<br>1/1 | REVISION<br>A0 |

|                                               |             |      |         |          |                        |      |
|-----------------------------------------------|-------------|------|---------|----------|------------------------|------|
|                                               |             |      |         |          | ANGLAR                 | ±5°  |
| ΔX                                            |             |      |         |          | L≤ 4                   | ±0.2 |
| ΔX                                            |             |      |         |          | 4<L≤ 16                | ±0.3 |
| ΔX                                            |             |      |         |          | 16<L≤ 63               | ±0.4 |
| MARK                                          | DESCRIPTION | DATE | REVISED | APPROVED | L> 63                  | ±0.5 |
| REVISIONS                                     |             |      |         |          | UNSPECIFIED TOLERANCES |      |
| www.helloxkb.com www.helloxkb.cn www.xk-dg.cn |             |      |         |          |                        |      |

**XKLB**

XKB INDUSTRIAL PRECISION CO.,LIMITED