






REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.06.25	阿树



Rated range:50mA DC12V
Insulation resistance:≥100MΩmin (DC100V)
Contact resistance:≤300mΩ
Compressive strength:AC100V(50/60Hzfof1minute)
Mechanical life:50000 cycles
Operating temperature:−10℃~+60℃
Operation strength:50±30gf



4	Button	1	PPA	black
3	Spring	1	Phosphorous copper	plate with silver
2	Welding foot	1	correrH62-0.2	silvery
1	Pedestal	1	PPA	black
ITEM	PAPT NAMF	QTY	Material	colour

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERAUCES	



DESIGN	阿树	VIEW:	MODEL TYPE:
CHECKED		UNIT: mm/in	Detect Switch
APPROVED		SIZE: A4	PART NO.:
			TM-1627S
			DWG NO.: