







PCB Layout

Specifications:

规格:

Voltage rating:125V AC/DC

额定电压: 125V AC/DC

Current rating:1A AC/DC

额定电流: 1A AC/DC

Withstanding voltage:250V AC/minute

耐受电压: 250V AC/分钟

Temperature range:-25℃~+85℃

温度范围: -25℃~+85℃

Insulation resistance:100MΩ min

绝缘电阻: 100MΩ Min

Contact resistance:20mΩ Max

接触电阻: 20mΩ Max

X9821 W V - 07 - N0 SN
① ② ③ ④ ⑤ ⑥

1.Series No

2.Category:W-Wafer

3.Welding Board Angle:V-Straight 180°

4.Row No.Pin No:XX-02~12P

5.Material:N0-PA66 ; 46-PA46 UL94V-0

6.Plating:SN-Tin Plated

Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
02	1.25	4.35	08	8.75	11.85
03	2.50	5.60	09	10.00	13.10
04	3.75	6.85	10	11.25	14.35
05	5.00	8.10	11	12.50	15.60
06	6.25	9.35	12	13.75	16.85
07	7.50	10.60	/		

X9821WV-07-N0SN	PA66	Phosphor Bronze	X9821H
PART NO	Material	Material(Pin)	Suitable XKB Housing

					ANGLAR	±5°
Δx					L≤ 4	±0.2
Δx					4<L≤ 16	±0.3
Δx					16<L≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L> 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						

XKB

XKB INDUSTRIAL PRECISION CO.,LIMITED

DSND	SCALE: N/A	MODEL TYPE: 1.25mm Crimp Style Connector	
DWN	VIEW:	PART NO.: X9821WV-07-N0SN	
CHKD	UNIT: mm/in	DWG NO.: X-X9821WV-07-N0SN	
APPD	SIZE: A4	WEIGHT	SHEET
			REVISION
		1/1	A0