




HSF



ROHS



Scale:2:1
PCB Layout Diagram
Top View

Note:

1. Material:

- a. Contact:C5191
- b. Surface Plating: Au

2. Electric:

- a. Contact Resistance:30 Mlliohms Max.
- b. Insulation Resistance:1000 Mega Ohms Min.
- c. Dielectnic Voltage:500 V AC One Sec Level
- d. Operating Temperature:-55° To +105°

Order code:

BS — M — G0 — R — CR151A
① ② ③ ④ ⑤

① BT:Battery Contacts ③ Contact Plating

② Apperance for the product

M: SMT TYPE

SN: Tin
G0: Gold flash
G1: 3U" Gold
G2: 5U" Gold
G3: 10U" Gold
G4: 15U" Gold
G5: 30U" Gold

④ Packing method


A: Tray packing
R: Tape & reel packing

⑤ Product number

CR151A

Unless Otherwise specified tolerance
X. ±0.35 X.XX: ±0.20
X.X: ±0.25 X.XXX: ±0.15

SCALE: As Shown UNIT: mm
DRAW Mo Guo Xuan DATE 13/03/2019
CHECK BobYang DATE 13/03/2019



Antenk® ANTENK ELECTRONICS CO., LTD
Http://www.antenk.com
E-mail:sales@antenk.com

TITLE: Battery Contacts For CR151

DRAWING NO: BS-M-G0-R-CR151A

PRODUCT NO: BS-M-G0-R-CR151A

REV	DESCRIPTION	DATE
1		
2		
3		
4		
5		