




1

2

3

4

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2024.12.16	阿树





Specifications:
Voltage rating:50V AC/DC
Current rating:2A AC/DC
Withstanding voltage:500V AC/minute
Temperature range:-40℃~+125℃
Insulation resistance:≥100MΩ MIN
Contact resistance:20mΩ MAX
After environmental testing: 20mΩ Max

A

A

B

B



PART NO.:



X1203 W R S-06-LP V01
① ② ③ ④ ⑤ ⑥ ⑦

- ①Series No
②Category:W-Wafer
③Welding Board Angle:R-Straight 90°
④Welding Way: S-SMT
⑤Row No.Pin No:XX-02~03Pin
⑥Material:N0-PALP LCP
⑦Plating Category: V01-All Gold Flash

Poles	Dimensions(mm)				
	A	B	C	D	E
02	1.20	2.70	4.20	3.20	1.50
03	2.40	3.90	5.40	4.40	1.50

C

C



剖面 A-A

D

D

X1203WRS-06-LPV01	N0-PA6T 94V-0	Phosphor Bronze	Gold Flash	X1203H
PART NO	Material	Material(pin)	Finish(pin)	Suitable XKB Housing
DESIGN	阿树	VIEW:	MODEL TYPE: 1.20mm Crimp Style Connectors	
CHECKED		UNIT: mm/in	PART NO.: X1203WRS-06-LPV01	
APPROVED		SIZE: A4	DWG NO.: X-X1203WRS-06-LPV01	
SCALE	N/A	PAGE	1/1	REVISION
				A1

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



XKB INDUSTRIAL PRECISION CO.,LIMITED

1

2

3

4