




REVISION RECORD				
REV	ECN.	DESCRIPTION	DRFT	DATE

NOTE 1:
UL标准(UL Standard)
1. 额定电压与电流: 300V/15A
Rated voltage/Rated current:300V/15A
2. 功频耐压: AC1600V/Min
Withstanding Voltage:AC1600V/Min
3. 线径范围: 28~12AWG
Wire range:28~12AWG
IEC标准(IEC Standard)
1. 额定电压与电流: 450V/20A
Rated voltage/Rated current: 450V/20A
2. 线径范围: 0.5~2.5mm²
Wire range : 0.5~2.5mm²
NOTE 2:
1. 间距(Pitch): 7.62mm
2. 使用温度范围: -40℃~+105℃
Operating temperature: -40℃~+105℃
3. 剥线长度: 7~8mm
Stripping length: 7~8mm
4. 符合RoSH环保要求
RoHS Compliance
5. 额定扭矩:4.43[Lb. in]
(Rated torque):4.43[Lb. in]
6. 未标注公差表
Undimensioned tolerances

P距方向公差 (mm)		其他尺寸公差 (mm)					
Pitch range in mm		Nominal dimension range in mm					
≤6	6~10	10~24	≤30	30~60	60~100	100~150	>150
±0.15	±0.20	±0.30	±0.20	±0.30	±0.50	±0.70	±1.00

订购方式(HOW TO ORDER)
MX2EDGK-7.62-□□P-□-□-□□□□

型号 间距 极数 客户型号
Series NO. Pitch Poles Customer Request

- 颜色(Color)
1. 灰色(Gray) 2. 蓝色(Blue)
3. 黑色(Black) 4. 绿色(Green)
5. 橙色(Orange) 6. 红色(Red)
7. 黄色(Yellow) 8. 白色(White)
9. 透明(Transparent)

4	(Cage)方盒	(Copper alloy) 铜合金	(Ni plated)镀镍	PART NO.:	 安徽亿思特电子科技有限公司 ANHUI EAST ELECTRONIC TECHNOLOGY CO., LTD.			
3	(Contact)触点	(Copper alloy) 铜合金	(Sn plated)镀锡	APPD:				
2	(Screw)螺丝 M3.0	(Steel) 钢	(Zn plated)镀锌	CHKD:				
1	(Housing)塑件	PA66	UL94V-0	DRFT:				
ITEM	NAME OF PART	MATERIAL	NOTES	THIED ANGLE PROJECTION	型号	MX2EDGK-7.62-XXP-1X-XXAH		
					系列	MX2EDGK-7.62	页码	1/1
					图号	MX2EDGK762001	比例	1:1