






Poles	Dimensions (mm)		Poles	Dimensions (mm)	
	A	B		A	B
2*01	6.65	---	2*07	24.65	18.00
2*02	9.65	3.00	2*08	27.65	21.00
2*03	12.65	6.00	2*09	30.65	24.00
2*04	15.65	9.00	2*10	33.65	27.00
2*05	18.65	12.00	2*11	36.65	30.00
2*06	21.65	15.00	2*12	39.65	33.00

X3025WRS-2x08D-LPSW	LCP UL 94V-0	Brass	Matte fin	Brass	Tin-Plated	X3025H
X3025WRS-2x08D-LPG05			Ni 50u"Min; Sn:120u"Min; Contact Area Gold:5u" Min.			
X3025WRS-2x08D-LPSN			Tin-Plated			
PART NO	Material	Material(Pin)	Finish(Pin)	Material (Solder Tabs)	Finish (Solder Tabs)	Mates With XKB Housing

							DSND		DATE		SCALE: N/A	MODEL TYPE: 3.00 mm Crimp Style Connectors			
				XKB	ANGLAR	±5°	DWN		DATE		VIEW: 	PART NO.: X30 25WRS-2x08D-LPSW			
Δx					 4	±0.2	CHKD		DATE		UNIT: mm/in	DWG NO.: X30 25WRS-2x08D-LPSW			
Δx					4<L>16	±0.3									
Δx					16<L>63	±0.4	APPD		DATE		SIZE: A4				
MARK	DESCRIPTION			DATE	REVISED	APPROVED							L>63	±0.5	
REVISIONS							UNSPECIFIED TOLERANCES			XKB INDUSTRIAL PRECISION CO.,LIMITED			WEIGHT 1.0g	SHEET 1/1	REVISION A0
www.helloxkb.com															