






	REVISIONS				
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.05.26	阿树



Code-x	H
A	2.50
B	3.10
C	3.40
D	3.70
E	4.30
F	5.00



SCHEMATIC

主要技术参数、性能

The Main Technology Performance

额定电流、电压:50mA DC12V

Rate voltage,current:50mA DC12V

接触电阻:≤100mΩ

Contact resistance:≤100mΩ

按力:50gf

Operating force:50gf

行程:0.25+ 0.10mm

Travel:0.25+ 0.10mm

绝缘电阻: ≥100MΩ

Insulated resistance: ≥100MΩ

介电强度: ≥250VAC/1min

Dielectric strength: ≥250VAC/1min

PAPT NO	TC-1157-B-D
Operating Force	A:100gf B:160gf C:260gf
Height	Code-X

⑤	Terminal	4	Brass (0.30t)	Plating silvering
④	Contact	1	F.ag/SUS	Natural
③	Base	1	PPA	
②	Cover	1	Spcc	Plating Nickel
①	Keystone	1	PPA	
ITEM	PAPT NAMF	QTY	MATERIAL	FINISHING

AuGLAR	$\pm 5^\circ$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED TOLERAUCES	

XK13 星城 Connection

DESIGN	阿树	VIEW:		MODEL TYPE: TACT SWITCH		
CHECKED		UNIT: mm/in		PART NO.: TC-1157-B-D		
APPROVED		SIZE: A4		DWG NO.: TC-1157-B-D		
PRECISION CO.,LIMITED				SCALE N/A	PAGE 1/1	REVISION A1