




SCHEMATIC

SS24E01- L5

L(MM)
2 ~10



RATING	0.3A 50V DC
CIRCUIT	1P2T
CONTACT RESISITANCE	100MΩ MAX
TRAVEL	2MM
OPERATING FORCE	250±100gf
OPERATING LIFE	10000

										DSND		DATE		SCALE: N/A	MODEL TYPE: SLIDE SWITCH		
Δx								units: mm	DWN		DATE		VIEW: 	PART NO.: SS24E01L5			
Δx								X.X ±0.2mm	CHKD		DATE		UNIT: mm/in	DWG NO.: X-SS24E01L5			
Δx								X.XX ±0.1mm	APPD		DATE		SIZE: A4				
MARK	DESCRIPTION				DATE	REVISED	APPROVED	X.XXX ±0.05mm									
REVISIONS								UNSPECIFIED TOLERANCES		XKB INDUSTRIAL PRECISION CO.,LIMITED				WEIGHT	SHEET	REVISION	
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn														1.0g	1/1	A0	