

1

2

3



4

A

B

C

D



产品字码标识

www.helloxkb.com www.helloxkb.cn www.xk-dg.cn

ANGULAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2024.05.09	桑 葚




规格 Specification:

- 额定值 Rating: 3A 125/250VAC
- 接触电阻 Contact resistance: $\leq 30\text{ m}\Omega$
- 绝缘电阻 Insulation resistance: $\geq 100\text{ M}\Omega$ (DC500V/Min)
- 电气寿命 Electronics life: > 10000 cycles
- 操作力 Operation force: $500 \pm 150\text{ gf}$
- 所有材料符合Rohs要求 All materials are Rohs compliant

PART NO.:

SS-X 03 23 S G-10 R 2 B B
① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨ ⑩ ⑪

- ① SS: XKB Vertical handle;
- ② Enclosure Material:
A-Metal case;
BLANK-Plastic case;
- ③ Current Rating: 03-3A;
- ④ Switch Circuit: 23-2P3T;
- ⑤ S: Wire bonding;
- ⑥ Handle Shape: G-Camber handle;
- ⑦ Handle Height: 3~15mm;
- ⑧ Enclosure Shape: R-Locking rings enclosure;
- ⑨ Terminal specs:
1:TYPE-1; 2:TYPE-2; 3:TYPE-3;
4:TYPE-4; 5:TYPE-5;
- ⑩ Handle Colour:
B-Black; W-White; R-Red
- ⑪ Housing Colour:
B-Black; W-White; R-Red



XKB INDUSTRIAL PRECISION CO.,LIMITED

DESIGN	桑 葚	VIEW: 	MODEL TYPE: SLIDE SWITCH		
CHECKED		UNIT: mm/in	PART NO.: SS-0323SG-10R2BB		
APPROVED		SIZE: A4	DWG NO.: X-SS-0323SG-10R2BB		
PRECISION CO.,LIMITED			SCALE	PAGE	REVISION
			N/A	1/1	A0

1

2

3

4

A

B

C

D