

REVISIONS				
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE
A1	N/A		图面升级整理图面	2025.06.16
A2	N/A	②X3	产品尺寸及材质变更	2025.10.17

A

B

C







D

A

B

C

D




SK13D07L5B

L(mm)	Colour
2~12	B:Black
	R:Red

- Specifications(规格):
- 1.Voltage rating(额定电压):DC 50V
 - 2.Current rating(额定电流):0.3A AC/DC
 - 3.Withstanding voltage(耐压值):≥500V AC/minute
 - 4.Insulation resistance(绝缘电阻):≥100MΩ Min
 - 5.Contact resistance(接触电阻):≤30mΩ Max
 - 6.Mating cycles(使用寿命): 10000 cycles Min
 - 7.Operating forceE(操作力): T1-T2:250±100 T2-T3:300±100
 - 8.Temperature range(使用温度):-25℃~+85℃

6	H piece	1	Phosphor bronze	Natural
5	Contact piece	1	Phosphor bronze	ag Plated
4	Terminal	4	Brass	ag Plated
3	Base	1	KB Cold Rolled Sheet	Yellow
2	Shell	1	Sus	Electric
1	Plastic	1	POM	Black
ITEM	PAPT NAME	QTY	MATERIAL	FINISHING



AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERAUCES	



DESIGN	阿树	VIEW:	MODEL TYPE: SLIDE SWITCH
CHECKED		UNIT: mm/in	PART NO.: SK13D07L5B
APPROVED		SIZE: A4	DWG NO.: X-SK13D07L5B