

REVISIONS				
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE
A2	ECN-P-202406005		新开模具, 尺寸参照修正	2024.06.21
A3	ECN-P-2026041401		产品外观变更	2026.04.14

Specifications(规格):

- 1.Voltage rating(额定电压):250V AC DC
- 2.Current rating(额定电流):7.0A AC/DC
- 3.Withstanding voltage(耐压值): $\geq 1500V$ AC/minute
- 4.Insulation resistance(绝缘电阻):1000M Ω Min
- 5.Contact resistance(绝缘电阻):10m Ω Max
- 6.Temperature range(使用温度):-40℃~+105℃

Material(材质):

- 1.Pin material: Brass
- 2.Finished: Tin 60u"
- 3.Housing material: PA46, UL94V-0
- 4.Housing color: Primary color

3D VIEW

PART NO.:

X9396 W V-12-46 SN
① ② ③ ④ ⑤ ⑥

- ①Series No
②Category:W-Wafer
③Welding Board Angle:V-Stright 180°
④Row No.Pin No:XX-02~15Pin
⑤Material:46-PA46 UL94V-0
⑥Planting: V01-Gold 1u"
SN-Bright tin plating

Poles	DIM.A	DIM.B
02	3.96	7.92
03	7.92	11.88
04	11.88	15.84
05	15.84	19.80
06	19.80	23.76
07	23.76	27.72
08	27.72	31.68
09	31.68	35.64
10	35.64	39.60
11	39.60	43.56
12	43.56	47.52
13	47.52	51.48
14	51.48	55.44
15	55.44	59.40

PCB LAYOUT

AuGLAR	$\pm 5^\circ$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED TOLERANCES	



DESIGN	山楂	VIEW:		MODEL TYPE:	3.96mm Crimp Style Connector
CHECKED		UNIT:	mm/in	PART NO.:	X9396WV-12-46SN
APPROVED		SIZE:	A4	DWG NO.:	

XKB INDUSTRIAL PRECISION CO.,LIMITED

SCALE	PAGE	REVISION
N/A	1/1	