





REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		pin B	2024.08.15	




- SPECIFICATIONS
- Voltage rating:250V AC/DC
 - Current rating:7A AC/DC
 - Withstanding Voltage:1500V AC/minute
 - Temperature range:-45°C~+125°C
 - Insulation resistance:≥ 1000MΩ
 - Contact resistance:≤10mΩ
 - After environmental testing:≤20mΩ

PART NO.:
X9396 H-05-N0

Series No
Category:H-HSG
Row No-Pin No XX-Q2P~15P
Material:N0-PA66 94V-0



Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
02	3.96	8.30	09	31.68	36.30
03	7.92	12.30	10	35.64	40.30
04	11.88	16.30	11	39.60	44.30
05	15.84	20.30	12	43.56	48.30
06	19.80	24.30	13	47.52	52.30
07	23.76	28.30	14	51.48	56.30
08	27.72	32.30	15	55.44	60.30



AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



X9396H-05-N0		Nylon 66 UL 94V-0	X9396T	X9396W
PART NO		Material	Suitable XKB Terminal	Suitable XKB Terminal
DESIGN		VIEW:	MODEL TYPE: 3.96mm Crimp Style Connectors	
CHECKED		UNIT: mm/in	PART NO.: X9396H-05-N0	
APPROVED		SIZE: A4	DWG NO.:	