







REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A			2025.12.04	



Specifications:
Voltage rating:50V AC/DC
Current rating:2A AC/DC
Withstanding voltage:500V AC/minute
Temperature range:-40 ~+125
Insulation resistance:≥100MΩ MIN
Contact resistance:20mΩ MAX
After environmental testing 20mΩ Max

PART NO.:
X1203 W R S-04-LP V01
Series No
Category:W-Wafer
Welding Board Angle:R-Stright 90°
Welding Way: S-SMT
Row No.Pin No:XX-04~06Pin
Material:LP-LCP UL94V-0;
Plating Category: V01-All Gold Flash

Poles	Dimensions(mm)			
	A	B	C	D
04	3.60	6.60	5.80	5.00
05	4.80	7.80	7.00	6.20
06	6.00	9.00	8.20	7.40

X1203WRS-XX-LPV01	LP-LCP 94V-0	Phosphor Bronze	Gold Flash	X1203H
PART NO	Material	Material(pin)	Finish(pin)	Suitable XKB Housing

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	VIEW:	MODEL TYPE: 1.20mm Crimp Style Connectors
CHECKED	UNIT: mm/in	PART NO.: X1203WRS-04-LPV01
APPROVED	SIZE: A4	DWG NO.: